


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	01/30/2015	DRAWING RELEASED	39056	DD	BSB



NOTES:

1. APPROXIMATE AMP RATING: 340A INDOOR, 405A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 4 LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.
5. APPROXIMATE WEIGHT: 1.684 LBS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: 50053102	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BE18T12TN	
CANADA:		DRAWN BY: M SUBRAMANI 11/10/2014	
1-800-361-6975 (QUEBEC)		CHECKER: B MANIKANDAN 11/10/2014	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: L TROMBLEY 2/7/2015	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: M STEVENS 2/4/2015	
		QA APRVL: C LINDQUIST 2/5/2015	
		MKT APRVL: K ROBICHEAU 2/4/2015	
PROD FAM:	DRAWING NO	REV	
PROJECT #:	SIZE	50053103	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			