


DRAWING NO.
50066754

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	07/24/2009 13:55:00 PM	CREATE A STAND ALONE SALE'S DRAWING FOR S2R496ACG1 - 27005077	40639	BM	RL



NOTES:

- 1 MATERIAL:
CAST ALUMINUM ALLOY
- 2 ACCOMMODATES:
3640 KCMIL (2.200 [56] DIA) ALUMINUM CABLE
- 3 NOMINAL BOLT INSTALLATION TORQUE:
5/8" GALVANIZED STEEL HARDWARE - 660 LB-IN [75 Nm]
- 4 DIMENSIONS IN BRACKETS [] DENOTES METRIC UNITS [SI UNITS]
AND ARE ROUNDED TO THE NEAREST WHOLE NUMBER. UNLESS
OTHERWISE SPECIFIED THESE UNITS SHALL BE USED FOR
REFERENCE ONLY.
- 5 PENETROX NOTE: SCRATCH BRUSH CONNECTOR CONTACT SURFACE DRY,
THEN APPLY PENETROX A. PENETROX CAN BE PURCHASED FROM BURNDY
LLC. IN CANS OR PLASTIC SQUEEZE BOTTLES.
- 6 THE CONCEPT SHOWN INCORPORATES PRINCIPLES WHICH PERMIT OPERATION
AT A VOLTAGE GRADIENT NORMALLY ASSOCIATED WITH 138 KV RMS
OPERATION PHASE TO PHASE.
- 7 HEX BOLTS CAPTURED TO PREVENT TURNING DURING INSTALLATION.
- 8 MARKING:
BURNDY
S2R496ACG1
3640 KCMIL ASC

(2) 5/8" DIA. HEX. GALVANIZED STEEL BOLTS, SPLIT LOCKWASHERS AND GALVANIZED STEEL NUTS.

TO ORDER BURNDY® PRODUCTS CALL		RIGID SPACER	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 27005077	CAT. NO: S2R496ACG1
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: BM 12/16/15	CHECKER: R LAVOIE 12/23/15
FOR PRODUCT INFO: http://www.burndy.com		DSN APPVL: R LAVOIE 12/23/15	MFG APPVL: T WAWRZYNIAK 12/28/15
		QA APPVL: C KOWALCZYK 12/30/15	MKT APPVL: --
		PROJ #: --	SCALE: 1:1
		SIZE: D	DRAWING NO: 50066754
		DOCUMENT TYPE: Sales	REV: A
		REL LEVEL: Released	SHEET 1 OF 1

REV: PEO200