CATALOG NUMBER	DESCRIPTION	CHARGER CATALOG NO.
PAT4PC834L5	PATRIOT® 4PC834 WITH 120V CHARGER	PATCHGRLI
PAT4PC834L5DC	PATRIOT® 4PC834 WITH 12V CHARGER	PATCHGRLIDC
PAT4PC834L5LCB	PATRIOT® 4PC834 LESS CHARGER AND BATTERY	PATCHGRLIDC

## SPECIFICATIONS:

OUTPUT FORCE: 6 TONS (5.4 METRIC TONS)

TOOL WEIGHT WITH BATTERY: 13.2 LBS (5.9 kg) LENGTH: 15.6 IN (39.6 cm) WIDTH: 3.2 IN (8.1 cm)

> HEIGHT: 14.1 IN (35.8 cm) OPERATING VOLTAGE: 18V-DC RECHARGE TIME: 45 MINUTES

## FOR USE ON:

COPPER: #8 - 1000 kcmil TERMINALS: YA, YA-L

COPPER: #8 - 500kcmil SPLICES: YS, YS-L, YS-T, YS-R

COPPER FLEX: #8 - 777.7 kcmil TERMINALS: YA-FX. YA-V

FIFX (750 NOMINAL) TERMINALS: YA-L-FX

SPLICES: YS. YS-LB, YSV-FXB

ALUMINUM: #8 - 750 kcmil TERMINALS: YA-A SPLICES: YS-A HYPLUG AYP, AYPO ALUMINUM: #8 - 750 kcmil

## FEATURES AND BENEFITS

- REFINED HYDRAULIC SYSTEM FOR ULTRA PERFOMANCE, SPEED AND RELIABILITY.

- FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHEST ENVIRONMENTS.

- OVERMOLDED HANDLE FOR COMFORT AND IMPROVED GRIP; ALLOWS FOR ONE HANDED

OPERATION FOR ADVANCE RETRACT AND HOLD.

- MAKITA 18 VOLT LITHIUM-ION BATTERIES PROVIDE 2.5 TIMES MORE CHARGE/DISCHARGE CYCLES THAN TRADITIONAL Ni-Cd BATTERIES AND PROVIDE 430% MORE LIFETIME WORK.

- MAKITA CHARGER CONTROLS CURRENT, VOLTAGE AMD TEMPERATURE TO MAXIMIZE BATTERY LIFE.

- FORCED AIR COOLING FAN COOLS THE BATTERY BY FORCING COOL AIR THROUGH THE BATTERY'S BUILT IN AIR VENTS.

- DIELESS SYSTEM ELIMINATES THE NEED TO PURCHASE AND MAINTAIN DIES.

- DIELESS SYSTEM ALLOWS CONNECTORS AND SPLICES TO BECOME RANGE TAKING. - C-SHAPED HEAD DESIGN ROTATES 360° AND ALLOWS FOR EASY REMOVAL ON CONTINUOUS CONDUCTORS.

- ERGONOMICALLY BALANCED TOOL DESIGN EASES OPERATION AND HELPS LESSEN FATIGUE.

- DURABLE HIGH IMPACT FORMED CARRYING CASE PROVIDES SUPERIOR PROTECTION AND STORES ALL ACCESSORIES.


- 5 YEAR LIMITED WARRANTY ON THE TOOL

- LIFETIME WARRANTY ON INFINITY DRIVE®

- 3 YEAR LIMITED WARRANTY ON THE BATTERIES AND CHARGER.

## NOTES:

 $\sqcup$  READ AND FOLLOW ALL INSTRUCTIONS PROVIDED BY THE OPERATORS MANUAL AND WARNING LABEL BEFORE USING THIS TOOL.



- 2. TOOL ACCEPTS 18V MAKITA LITHIUM ION BATTERIES, BL SERIES OF SIZE 2.0 AHR AND GREATER IF THE PLASTIC BATTERY CLIP IN THE TOOL HAS A "STAR" MOLDED INTO IT. THE "STAR" IDENTIFIES ACCEPTANCE OF THE BL SERIES BATTERIES.
- 3. FOR TOOLS WHICH DO NOT HAVE A "STAR" MOLDED INTO THE PLASTIC BATTERY CLIP, USE IS LIMITED TO THE BL 1830 (3.0 AHR) BATTERY. FORCING ANY OTHER BATTERY INTO THIS TOOL WILL VOID THE WARRANTY.



PATRIOT® 4 POINT C-HEAD DIELESS TOOL TO ORDER BURNDY® PRODUCTS CALL ITEM NO: --UNITED STATES: I-800-346-4175 (LONDONDERRY, NH) e: Burndy CANADA: I-800-36I-6975 (QUEBEC) I-800-387-6487 (ALL OTHER PROVINCES) DRAWING NO REV 50068026 FOR PRODUCT INFO: http://www.burndy.com SHEET LOF L