



WILEY-ROPELAY BONDING JUMPER (WILEY-RLJ6C--38)		
ITEM NUMBER	CATALOG NO.	LENGTH "L"
50101262	WILEY-RLJ6C6-38	152.4 [6]
50101263	WILEY-RLJ6C12-38	304.8 [12]
50101264	WILEY-RLJ6C18-38	457.2 [18]
50123251	WILEY-RLJ6C24-38	609.6 [24]
50123252	WILEY-RLJ6C30-38	762.0 [30]
50123253	WILEY-RLJ6C36-38	914.4 [36]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	05/24/2021	CATALOG # WILEY-RLJ6C24-38, WILEY-RLJ6C30-38, WILEY-RLJ6C36-38 ADDED TO THE TABLE	210524008434	PB	RG



NOTES:

- MATERIAL:
HYLUG: TIN PLATED COPPER
ROPELAY JUMPER: TIN PLATED COPPER (6 AWG).

2 FACTORY INSTALLATION.

- DIMENSIONS IN BRACKETS [] ARE IN INCHES ROUNDED OFF TO THE NEAREST HUNDREDTH, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-387-6487

FOR PRODUCT INFO: <http://www.burndy.com>

WILEY-ROPELAY BONDING JUMPER

ITEM NO: SEE TABLE

CAT. NO: SEE TABLE

DRAWN BY: B.PARTHIBAN 06/07/2019

CHECKER: E.MARTIN 10/26/2019

DSN APRVL: E.MARTIN 10/26/2019

MFG APRVL: 10/28/2019

QA APRVL: B.ELLIOTT 10/28/2019

MKT APRVL: S.PARSONS 10/26/2019

PROD FAM: WILEY

PROJECT #: SALES

REL LEVEL: Released



DRAWING NO

50101196

SHEET 1 OF 1

REV

B