



CATALOG NO.	NUMBER OF CONDUCTORS	NUMBER OF MTG HOLES	W	HEX SIZE
KK6A39U6S	6.00	6.00	4.75	5/16
KK8A39U8S	8.00	8.00	6.50	5/16
KK12A39U10S	12.00	10.00	8.25	5/16

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	04/28/21	NEW DRAWING CREATED	210416007293	JL	TR



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
2. THIS DRAWING TO BE INTERPRETED PER ASME Y14.5
3. MATERIAL: CLEAR PLATED ALUMINUM
4. #2 AWG TO 750 Kcmil CLASS B & C.
5. AVAILABLE WITHOUT PENETROX OXIDE INHIBITOR. ADD SUFFIX "NP" TO CATALOG NUMBER (EXAMPLE: KK6A39U6SNP)

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-387-6487
 FOR PRODUCT INFO: <http://www.burndy.com>

TRANSFORMER TERMINAL	
ITEM NO: SEE TABLE	
CAT. NO: SEE TABLE	
DRAWN BY: J.L. BERGERON	4/28/2021
CHECKER: T. REYNOLDS	4/28/2021
DSN APRVL: A. STOKES	8/31/2021
MFG APRVL: J. NEAR	8/31/2021
QA APRVL: T. WATTS	8/31/2021
MKT APRVL: M. TWEH	8/31/2021
PROD FAM: --	DRAWING NO
PROJECT #: --	50121290
DOCUMENT TYPE: SALES	SIZE
REL LEVEL: Released	B
	REV
	A
SHEET 1 OF 1	

