



ITEM NUMBER	CATALOG NUMBER	LENGTH "L"	HOLE SIZE	HOLE DIAMETER "K DIA."	ITEM NUMBER	CATALOG NUMBER	LENGTH "L"	HOLE SIZE	HOLE DIAMETER "K DIA."
50121842	BB049ML6T14TN	6.00 [152]	1/4"	.27 [7]	50121849	BB049ML24T38TN	24.00 [610]	3/8"	.41 [11]
50121843	BB049ML9T14TN	9.00 [229]	1/4"	.27 [7]	50125944	BB049ML12T12TN	12.00 [305]	1/2"	.56 [56]
50121844	BB049ML12T14TN	12.00 [305]	1/4"	.27 [7]					
50122748	BB049ML18T14TN	18.00 [457]	1/4"	.27 [7]					
50121845	BB049ML24T14TN	24.00 [610]	1/4"	.27 [7]					
50121846	BB049ML6T38TN	6.00 [152]	3/8"	.41 [11]					
50131904	BB049ML8T38TN	8.00 [203]	3/8"	.41 [11]					
50121847	BB049ML9T38TN	9.00 [229]	3/8"	.41 [11]					
50121371	BB049ML12T38TN	12.00 [305]	3/8"	.41 [11]					
50121848	BB049ML18T38TN	18.00 [457]	3/8"	.41 [11]					

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	02/24/2023	ADDED 8" BRAID PER FOCUS FPN2302090.	230224028177	PC	NB



NOTES:

- MATERIAL : FERRULES - TINNED COPPER
BRAID - TINNED COPPER : 49 KCMIL [25 MM²]
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 ALL SIZES ARE cULus LISTED TO UL 467 AND CSA C22.2 NO. 41 GROUND AND BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-387-6487
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID		DRAWING NO		REV	
ITEM NO: SEE TABLE		50121362		D	
CAT. NO: SEE TABLE		50121362		D	
DRAWN BY: B.PARTHIBAN	3/1/2021	50121362		D	
CHECKER: S.CARBONNEAU	10/6/2021	50121362		D	
DSN APRVL: S.CARBONNEAU	10/6/2021	50121362		D	
MFG APRVL: E.VARGAS	10/25/2021	50121362		D	
QA APRVL: --		50121362		D	
MKT APRVL: K.ROBICHEAU	10/7/2021	50121362		D	
PROD FAM: MECHANICAL GROUNDING		50121362		D	
PROJECT #: --	SIZE	50121362		D	
DOCUMENT TYPE: SALES		50121362		D	
REL LEVEL: Released	B	50121362		D	

