



ITEM NUMBER	CATALOG NUMBER	LENGTH "L"	HOLE SIZE	HOLE DIAMETER "K DIA."
50122732	BB099ML6T38TN	6.00 [152]	3/8"	.41 [11]
50122733	BB099ML9T38TN	9.00 [229]	3/8"	.41 [11]
50121375	BB099ML12T38TN	12.00 [305]	3/8"	.41 [11]
50127023	BB099ML14D50T38TN	14.50 [368]	3/8"	.41 [11]
50131584	BB099ML15T38TN	15.00 [381]	3/8"	.41 [11]
50122749	BB099ML18T38TN	18.00 [457]	3/8"	.41 [11]
50122734	BB099ML24T38TN	24.00 [610]	3/8"	.41 [11]
50122735	BB099ML9T12TN	9.00 [229]	1/2"	.53 [14]
50122736	BB099ML12T12TN	12.00 [305]	1/2"	.53 [14]
50122737	BB099ML18T12TN	18.00 [457]	1/2"	.53 [14]
50122738	BB099ML24T12TN	24.00 [610]	1/2"	.53 [14]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	10/11/2022	NOTES UPDATED	221010024669	PC	SC



NOTES:

- MATERIAL : FERRULES - TINNED COPPER
BRAID - TINNED COPPER : 99 KCMIL [50 MM²]
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 ALL SIZES ARE cULus LISTED TO UL 467 AND CSA C22.2 NO. 41 GROUND AND BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE CAT. NO: SEE TABLE	
CANADA: 1-800-387-6487		DRAWN BY: B.PARTHIBAN 3/1/2021	
FOR PRODUCT INFO: http://www.burndy.com		CHECKER: S.CARBONNEAU 10/6/2021	
		DSN APRVL: S.CARBONNEAU 10/6/2021	
		MFG APRVL: E.VARGAS 10/25/2021	
		QA APRVL: --	
		MKT APRVL: K.ROBICHEAU 10/7/2021	
		PROD FAM: MECHANICAL GROUNDING	
		PROJECT #: --	
		SIZE	
		50121366	
		REV	
		D	
		REL LEVEL: Released	
		SHEET 1 OF 1	

