



ITEM NUMBER	CATALOG NUMBER	LENGTH "L"	HOLE SIZE	HOLE DIAMETER "K DIA."
50121376	BB139ML12T38TN	12.00 [305]	3/8"	.41 [11]
50131585	BB139ML15T38TN	15.00 [381]	3/8"	.41 [11]
50122751	BB139ML18T38TN	18.00 [457]	3/8"	.41 [11]
50122739	BB139ML24T38TN	24.00 [610]	3/8"	.41 [11]
50122740	BB139ML12T12TN	12.00 [305]	1/2"	.53 [14]
50122741	BB139ML18T12TN	18.00 [457]	1/2"	.53 [14]
50122742	BB139ML24T12TN	24.00 [610]	1/2"	.53 [14]
50127792	BB139ML12T34TN	12.00 [305]	3/4"	.78 [20]
50140098	BB139ML24T34TN	24.00 [610]	3/4"	.78 [20]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	04/18/2023	UPDATE AS PER MARKUP	230417029641	PC	SC



NOTES:

- MATERIAL : FERRULES - TINNED COPPER
BRAID - TINNED COPPER : 139 KCMIL [70 MM²]
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 ALL SIZES ARE cULus LISTED TO UL 467 AND CSA C22.2 NO. 41 GROUND AND BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-387-6487
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO: SEE TABLE	
CAT. NO: SEE TABLE	
DRAWN BY: B.PARTHIBAN	3/1/2021
CHECKER: S.CARBONNEAU	10/6/2021
DSN APRVL: S.CARBONNEAU	10/6/2021
MFG APRVL: E.VARGAS	10/25/2021
QA APRVL: --	
MKT APRVL: K.ROBICHEAU	10/7/2021
PROD FAM: MECHANICAL GROUNDING	DRAWING NO
PROJECT #: --	SIZE
DOCUMENT TYPE: SALES	50121367
REL LEVEL: Released	B
	SHEET 1 OF 1



REV
D