



COVER RANGE TABLE *			REV.	DATE	DESCRIPTION	BY	C'K'D.
METRIC WIRE SIZES			2	12/15/93	REDRAWN TO CAD. ADDED METRIC WIRE SIZES PER (PCN 1512).	RDP	KM
COVER	EQUAL RUN & TAP	MIN TAP - MAX RUN					
KS25	25mm ² STR [6.5] - 50mm ² STR [9.3]	2.5mm ² STR [2.1] - 50mm ² STR [9.3]					
KS26	35mm ² STR [7.6] - 50mm ² STR [9.3]	2.5mm ² STR [2.1] - 70mm ² STR [10.9]					

* FOR REFERENCE ONLY



FRONT



BACK

NOTES:

- THE SC2/0 SERVIT INSULATING COVER ACCOMMODATES AND MEETS UL REQUIREMENTS FOR INSULATING THE FOLLOWING CONNECTORS:

BURNDY	KS25 & KS26
BLACKBURN	10H & 20H
DOSSERT	DS10F & DS13F
ILSCO	IL 1/0 & IL 2/0
PENN UNION	S1/0S & S2/0S
- THE SC2/0 SERVIT INSULATING COVER ALSO ACCOMMODATES:

BURNDY	KSA, 2KSA1/0
--------	--------------
- U.L. 486A LISTED, FILE NO. E9498
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS AND ARE FOR REFERENCE ONLY.

SERVIT INSULATING COVER			
CAT NO: SC2/0		SCALE FULL SIZE	
DRAWN: JHB	2/17/64	CHECKED: MJM	2/18/64
DSGN APPVL: ESR	2/18/64	MFG APPVL: .	
Q.A. APPVL: .		MKTG APPVL: .	
CAD FILE: SA55878-SHT01		PM REF: N/A	
BURNDY		MDL REF: N/A	
		PROJECT: .	
		DRAWING NO.	REV
		SA55878	2
SHEET 1 OF 1			

REV: 111991