


NOTES:

1. ALL DIMENSIONS ARE IN INCHES (mm) UNLESS OTHERWISE NOTED.
2. ALTITUDE = 0 - 12,000 FT (3657 m)
3. MCOV = 8.4 KV
4. RATED VOLTAGE = 10 KV
5. LEAKAGE DISTANCE = 14.4 IN (366 mm)
6. ARRESTER WEIGHT = 2.2 LBS (1 KG).

INSTALLATION NOTE: IF PRESENT, REMOVE METAL STRAP CONNECTED ACROSS DISCONNECTOR. STRAP IS FOR SHIPPING PURPOSES ONLY.

.5 μ SEC IR	10kA KV	500 A SWITCHING SURGE IR KV	MAXIMUM 8/20 DISCHARGE VOLTAGE - KV AT					
			1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
34		34.4	25.4	27.1	28.8	31.6	35.6	42.3

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.		HUBBELL® POWER SYSTEMS		
	TITLE PROTECTA LITE 8.4 KV MCOV			
REV DATE	SIZE	DWG NO.	CAT / PART / ASSY NO.	REV
06/03/16	S	--	602009-B0-X1-003	0
DO NOT SCALE THIS DRAWING		DRN BY RVK	DATE 06/03/16	SHEET 1 OF 1