



- NOTES:
1. ALTITUDE 0-12000 FT ABOVE SEA LEVEL.
  2. WEIGHT OF ARRESTER INCL HDV - 16 LBS.
  3. MAX CONTINUOUS LINE TO GROUND OPERATING VOLTAGE - 48 KV RMS.
  4. ARRESTER LEAKAGE DISTANCE - 81.4 IN.

.5 μ SEC 10KA IR K V	500 A SWITCHING SURGE IR K V	MAXIMUM 8/20 DISCHARGE VOLTAGE - KV AT											
		1.5 KA	3.0 KA	5 KA	10 KA	20 KA	40 KA	197.2	141.5	147.6	157.4	166.9	183.4

CONFER WITH THE DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE INFORMATION IS NOT TO BE DISCLOSED TO OTHERS WITHOUT THE WRITTEN PERMISSION OF HUBBEL POWER SYSTEMS. UNLESS OTHERWISE SPECIFIED, ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

**HUBBEL POWER SYSTEMS**  
TRADE MARK

TITLE: **PROTECTA LITE**  
48 KV MCOV

SIZE: B  
DWG NO.: 602048-D1-DE-001  
DWT / PART / ASSY NO.:  
DWN BY: JVR  
DATE: 05/25/10  
SHEET 1 OF 1

REV DATE: 05/25/10