


NOTES:

1. ALL DIMENSIONS ARE IN INCHES (mm) UNLESS OTHERWISE NOTED.
2. ALTITUDE = 0 - 12,000 FT (3657 m) ABOVE THE SEA LEVEL.
3. MCOV = 57 KV
4. RATED VOLTAGE = 72 KV
5. LEAKAGE DISTANCE = 98.7 IN (2507 mm)
6. ARRESTER WEIGHT = 20.0 LBS (9.1 kg).
7. DIMENSIONS SUBJECT TO ±3% TOLERANCE.
8. ONLY PACK THIS PART IN CRATES WITH 8 PIECES OR LESS.

INSTALLATION NOTE: IF PRESENT, REMOVE METAL STRAP CONNECTED ACROSS DISCONNECTOR. STRAP IS FOR SHIPPING PURPOSES ONLY.

.5 μ SEC IR KV	10kA KV	500 A SWITCHING SURGE IR KV	MAXIMUM 8/20 DISCHARGE VOLTAGE - KV AT					
			1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
236.1		169.4	176.6	188.4	199.8	219.5	246.8	293.8



HUBBELL® POWER SYSTEMS

TITLE
PROTECTA LITE
57 KV MCOV

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

SIZE S	DWG NO. --	CAT / PART / ASSY NO. 602057-X0-X1-001	REV 2
-----------	---------------	---	----------

REV DATE
02/13/20

DO NOT SCALE THIS DRAWING	DRN BY JVR	DATE 07/06/09	SHEET 1 OF 1
---------------------------	------------	---------------	--------------