



NOTES:

1. ALL DIMENSIONS ARE IN INCHES (mm) UNLESS OTHERWISE NOTED.
2. ALTITUDE = 0 - 12,000 FT (3657 m)
3. MCOV = 98 KV
4. RATED VOLTAGE = 120 KV
5. LEAKAGE DISTANCE = 163 in (4140 mm)
6. ARRESTER WEIGHT = 22.5 lbs (10.2 kg).

INSTALLATION NOTE: IF PRESENT, REMOVE METAL STRAP CONNECTED ACROSS DISCONNECTOR. STRAP IS FOR SHIPPING PURPOSES ONLY.

.5 μ SEC 10kA IR kV	500 A SWITCHING SURGE IR kV	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
394.4	283.0	295.2	314.8	333.8	366.8	412.6	491.0



HUBBELL® POWER SYSTEMS

TITLE
PROTECTA LITE
98 KV MCOV

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

SIZE S	DWG NO. --	CAT / PART / ASSY NO. 602098-A2-B6-002	REV 0
DO NOT SCALE THIS DRAWING	DRN BY RVK	DATE 08/17/17	SHEET 1 OF 1

REV DATE
08/17/17