



TYPE	CABLE SIZE		A	B	C	D	J
	BARE COPPER	GUY WIRE					
BC4C	#450L.	1/4	3/8	7/8	7/8	1 3/16	UB336
BC2C	#250L.	5/16	3/8	7/8	7/8	1 1/4	UB336
BC25	1/8 STR.	3/8	3/8	1 1/8	7/8	1 7/16	UB178
BC28	3/8 STR TO 1/2 STR	1/2	1/2	1 5/8	1 1/8	1 3/4	UB224
BC30	1/2 STR. TO 300MCM.	5/8	1/2	1 7/8	1 1/4	1 5/16	UB226
BC32	350 MCM TO 400 MCM	3/4	5/8	2 1/2	1 3/8	2 1/4	UB294
BC35	450 MCM TO 550 MCM	7/8	5/8	2 7/16	1 3/4	2 5/8	UB278
BC39	600 MCM TO 750 MCM	1"	3/4	2 5/16	1 13/16	2 13/16	UB332
BC44	800 MCM TO 1000 MCM	1 1/8	3/4	3 1/4	1 5/16	2 7/8	UB303

MATERIAL-
CAST COPPER ALLOY #115
(85% COPPER)

REFERENCE: SA7988M

NO.	DATE	REVISION	BY	CHKD	DESCRIPTION
7	5-6-75	BC25, 1 7/16 WAS 1 3/8 (DC 8595)	CARL	CAR	DEAD END CLIP
6	3-21-75	REV. REF. PRINT. (DC 8547)	T.M.	T.M.	
5	3-23-67	MATERIAL: ALLOY #115 WAS #330 (EC34441)	H.C.	E.W.B.	TYPE 'BC' GENL. DWG.
4	2-28-55	ON BC2C, UBS36 WAS UBS178 6" DIA. WAS 1 1/8" (EC10953)	M.W.	E.W.	DRAWN 6-26-40 W.A.B. CHECKED <i>W.A.B.</i>
3	1-25-54	UB178 PART OF BC2C, WAS UBS36 (EC10953)	E.W.	E.W.	DRAWING NO. SA-7988
2	1-16-48	U BOLT COLUMN ADDED (P.O.366)	D.M.	W.T.B.	SA-7988 7
1	6-5-47	BC26 REMOVED FROM TABLE, BC28 CABLE RANGE WAS 3/8-1/2 (EC1089)	B.K.	W.T.B.	

BURNDY

ORIGINAL