



DRY ARCING DISTANCE _____ 188 MM (7.4 IN)
 LEAKAGE DISTANCE _____ 279 MM (11.0 IN)
 60 Hz DRY FLASHOVER _____ 90 kV
 60 Hz WET FLASHOVER _____ 70 kV
 IMPULSE POS. CRITICAL FLASHOVER _____ 150 kV
 IMPULSE POS. WITHSTAND _____ 140 kV
 SCL _____ 12.5 kN (2800 LB)
 RCL _____ 5.5 kN (1235 LB)
 NET WEIGHT _____ 4.5 KG (9.9 LB.)

OHIO BRASS
TOLERANCE CHART



HUBBELL POWER SYSTEMS

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

TITLE
VERI LITE
15 KV LINE POST

REV DATE 08/21/07

SIZE S	DWG NO. --	CAT / PART / ASSY NO. 80S015-0100	REV 2
DO NOT SCALE THIS DRAWING		DRN BY JVR	DATE 08/31/05
			SHEET 1 OF 1