



DRY ARCING DISTANCE _____	244 MM (9.6 IN)
LEAKAGE DISTANCE _____	439 MM (17.3 IN)
60 Hz DRY FLASHOVER _____	110 kV
60 Hz WET FLASHOVER _____	75 kV
IMPULSE POS. CRITICAL FLASHOVER _____	185 kV
IMPULSE POS. WITHSTAND _____	170 kV
SCL _____	12.5 kN (2800 LB.)
RCL _____	5.5 kN (1235 LB.)
NET WEIGHT _____	4.7 KG (10.3 LB.)

CHIEF/BRASS
TOLERANCE CHART



HUBBELL POWER SYSTEMS

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

TITLE
VERI LITE
25 KV LINE POST

SIZE S	DWG NO. --	CAT / PART / ASSY NO. 80S025-0100	REV 3
-----------	---------------	--------------------------------------	----------

REV DATE 08/21/07	DO NOT SCALE THIS DRAWING	DRN BY JVR	DATE 08/31/05	SHEET 1 OF 1
----------------------	---------------------------	------------	---------------	--------------