



PCORE
ELECTRIC

KV CLASS 69 kV BIL 350 kV Uy 44 kV

CURRENT RATING

3000 AMP BOTTOM CONNECTION

DWG. CATALOG NUMBER GLAZE COLOR

SD B-88033-138 BROWN

SD B-88033-138-70 LT. GRAY

DATE 1-9-14 REV. DATE 4-17-20

MAXIMUM ALTITUDE 10000 ft [3000 m]

NET WEIGHT 235 lb [107 kg]

ANGLE OF INCLINATION FROM THE VERTICAL 0° TO 60°

MIN. CREEP 53.50 [1358.9] MIN. STRIKE 24.00 [609.6]



CREEP/L-G 1.34 [34.1] STD. IEEE C57.19.00/01

PCB CONTENT OF OIL IS LESS THAN 1 ppm


TITLE

POC BUSHING ASSEMBLY

2 1/2-12 THD. TOP AND BOTTOM TERM.,
.75 [19.1] LONGER ABOVE FLANGE
& .50 [12.7] LONGER BELOW FLANGE



MOUNTING FLANGE



**FLANGE ALIGNMENT DIAGRAM
TOP VIEW**

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION NET WEIGHT WAS 240 lbs, CORRECTED ROUNDING, CREEP/L-G WAS CREEP/Uy

SCALE 1/8

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER