



PCORE
ELECTRIC

KV CLASS 25 kV BIL 150 kV Uy 16 kV

CURRENT RATING

5000 AMP BOTTOM CONNECTION

MIN. CREEP 19.50 [495.3] MIN. STRIKE 11.00 [279.4]

CREEP/L-G 1.35 [34.3] STD. IEEE C57.19.00/01

PCB CONTENT OF OIL IS LESS THAN 1 ppm

DWG. CATALOG NUMBER GLAZE COLOR

SD B-88753-358 BROWN



SD B-88753-358-70 LT. GRAY

TITLE



POC BUSHING

HORIZONTAL MOUNTING WITH TANK
125°C INSULATION
TERMINAL BLADE IN-LINE WITH TANK

DATE	10-24-19	REV. DATE
MAXIMUM ALTITUDE	10000 ft [3000 m]	
NET WEIGHT	230 lb [104 kg]	
ANGLE OF INCLINATION FROM THE VERTICAL	60° TO 90°	



MOUNTING FLANGE



**FLANGE ALIGNMENT DIAGRAM
SHOWN HORIZONTALLY MOUNTED
TOP VIEW**

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION

SCALE 1/8

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER