



PCORE
ELECTRIC

kV CLASS 34.5 kV **BIL** 200 kV **Uy** 22 kV

CURRENT RATING

3000 AMP BOTTOM CONNECTION

DWG. **CATALOG NUMBER** **GLAZE COLOR**

SD	B-88833-321	BROWN
SD	B-88833-321-70	LT. GRAY

TITLE IEEE STANDARD BUSHING

POC BUSHING

Ø1.00 [25.4] HOLES ON 9.75 B.C.
3 1/4-12 THREAD BOTH ENDS
2.00 [50.8] LONGER ABOVE & BELOW FLANGE

DATE 5-12-5 **REV. DATE** 3-2-22

MAXIMUM ALTITUDE 3300 ft [1000 m]



NET WEIGHT 128 lb [58 kg]

ANGLE OF INCLINATION FROM THE VERTICAL 0° TO 60°

MIN. CREEP 30.50 [774.7] **MIN. STRIKE** 14.00 [355.6]

CREEP/L-G 1.53 [38.9] **STD.** IEEE C57.19.00

PCB CONTENT OF OIL IS LESS THAN 1 ppm



DIMENSIONS IN INCHES [MILLIMETERS]

REVISION CHANGED TERMINAL ADAPTOR TO TERMINAL ADAPTOR AND COLLAR

SCALE 1/6

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER