


MAY 17 1996

DWG. DATE 11-5-93		REV. DATE 5-8-98		TITLE		DWG.	CATALOG NUMBER	UPPER PORCELAIN GLAZE COLOR
MIN. CREEP 17.00 (432)		KV CLASS 15 KV		7.25 B.C. (184), AIR TO OIL		SD	B-89111-62	CHOCOLATE
CREEPAGE PER Uy 1.70 (43)		Uy 10 KV		HORIZONTAL MOUNTING WITH TANK		SD	B-89111-62-70	LT. GRAY No.70
MIN. STRIKE DIST. 9.50 (241)		BL 110 KV		TEST STANDARD IEEE		CURRENT RATING		
				NET WEIGHT 30 lbs.		1200 AMP BOTTOM CONNECTIONS		
				ANGLE INCLINATION FROM VERTICAL = 70° TO 90°		@ 95°C MAX. OIL TEMPERATURE		



3.00 (76) OVERHEAD CLEARANCE
REQUIRED TO REMOVE DIPSTICK


AUXILIARY OIL TANK,
OIL AND INSTALLATION
INSTRUCTIONS INCLUDED

OIL FILL
PLUG

TEST TAP

45°

FLANGE ALIGNMENT DIAGRAM
SHOWN HORIZONTALLY MOUNTED



MOUNTING FLANGE

Bk. No. 7A2A

DIMENSIONS IN INCHES (MILLIMETERS)

LAST REVISION ADDED CLEARANCE NOTE FOR DIPSTICK.

NOTE TO PURCHASER
ALL SALES OF LAPP PRODUCTS ARE
SUBJECT TO OUR STANDARD TERMS
AND CONDITIONS AND THE LIMITED
WARRANTIES THEREUNDER