



PCORE
ELECTRIC

kV CLASS 25 kV **BIL** 150 kV **Uy** 16 kV

CURRENT RATING

2000 AMP BOTTOM CONNECTION

DWG. **CATALOG NUMBER** **GLAZE COLOR**

SD	B-89221-46	BROWN
SD	B-89221-46-70	LT. GRAY



TITLE

PRC BUSHING


1 1/2-12 THD. TOP AND
BOTTOM TERMINALS

DATE	2-21-96	REV. DATE	4-22-19
MAXIMUM ALTITUDE	10000 ft [3000 m]		
NET WEIGHT	97 lb [44 kg]		
ANGLE OF INCLINATION FROM THE VERTICAL	0° TO 70°		

MIN. CREEP	27.50 [698.5]	MIN. STRIKE	14.00 [355.6]
CREEP/L-G	1.91 [48.4]	STD.	IEEE C57.19.00/01
PCB CONTENT OF OIL IS LESS THAN 1 ppm			



MOUNTING FLANGE



FLANGE ALIGNMENT DIAGRAM
TOP VIEW

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION REVISED PORCELAIN FOR MFG. REQUEST, CORRECTED ROUNDING, CREEP/L-G WAS CREEP/Uy

SCALE 1/6

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER