



PCORE
ELECTRIC

kV CLASS 25 kV **BIL** 150 kV **Uy** 16 kV

CURRENT RATING

2000 AMP BOTTOM CONNECTION

DWG. **CATALOG NUMBER** **GLAZE COLOR**



SD	B-89223-182	BROWN
SD	B-89223-182-70	LT. GRAY

TITLE PRC BUSHING


BLADE TYPE BOTTOM TERMINAL
1.56 [39.6] LONGER ABOVE FLANGE
2.81 [71.4] LONGER BELOW FLANGE
6 HOLES ON 9.25 [235.0] B.C.

DATE	7-13-94	REV. DATE	4-16-19
MAXIMUM ALTITUDE	10000 ft [3000 m]		
NET WEIGHT	102 lb [46 kg]		
ANGLE OF INCLINATION FROM THE VERTICAL	0° TO 70°		

MIN. CREEP	27.50 [698.5]	MIN. STRIKE	14.00 [355.6]
CREEP/L-G	1.91 [48.4]	STD.	IEEE C57.19.00
PCB CONTENT OF OIL IS LESS THAN 1 ppm			



MOUNTING FLANGE DETAIL



**FLANGE ALIGNMENT DIAGRAM
TOP VIEW**

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION REVISED PORCELAIN FOR MFG. REQUEST, CORRECTED ROUNDING, CREEP/L-G WAS CREEP/Uy

SCALE 1/5

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER