





PCORE
ELECTRIC


DATE	6-6-14	REV. DATE	6-24-14
MAXIMUM ALTITUDE	10000 ft [3000 m]		
NET WEIGHT	190 lb [86 kg]		
ANGLE OF INCLINATION FROM THE VERTICAL	0° TO 90°		

kV CLASS	34.5 kV	BIL	200 kV	Uy	22 kV
CURRENT RATING					
3000 AMP BOTTOM CONNECTION					
MIN. CREEP	41.00 [1041.4]	MIN. STRIKE	16.00 [406.4]		
CREEP/Uy	1.86 [47.3]	STD.	IEEE C57.19.00/01		
PCB CONTENT OF OIL IS LESS THAN 1 ppm					


DWG.	CATALOG NUMBER	GLAZE COLOR
SD	B-89331-830	BROWN
SD	B-89331-830-70	LT. GRAY
TITLE		
PRC BUSHING ASSEMBLY		
HORIZONTAL/VERTICAL MOUNTING, 2-12 THD. BOTH ENDS SHORTER BELOW FLANGE		



**OIL TANK DETAIL
SHOWN IN HORIZONTAL
MOUNTING POSITION**



MOUNTING FLANGE DETAIL



**FLANGE ALIGNMENT DIAGRAM
TOP VIEW**

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION REMOVED PRELIMINARY DRAWING NOTE

SCALE 1/6

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER