

WWW.PCOREELECTRIC.COM



PCORE

ELECTRIC


DATE	12-10-08	REV. DATE	
MAXIMUM ALTITUDE	10000 ft [3000 m]		
NET WEIGHT	82 lb [37 kg]		
ANGLE OF INCLINATION FROM THE VERTICAL	0° TO 70°		

KV CLASS	34.5 kV	BIL	200 kV	Uy	22 kV
CURRENT RATING					
1200 AMP BOTTOM CONNECTION					
MIN. CREEP	41.00 [1041.4]	MIN. STRIKE	17.00 [431.8]		
CREEP/Uy	1.86 [47.3]	STD.	IEEE C57.19.00/01		
PCB CONTENT OF OIL IS LESS THAN 1 ppm					


DWG.	CATALOG NUMBER	GLAZE COLOR
SD	B-89393-216	BROWN
SD	B-89393-216-70	LT. GRAY
TITLE		
PRC BUSHING		
QUICK LINK BOTTOM CONNECTION JOINT .75 [19.0] ABOVE FLANGE MOUNTING SURFACE SILVER PLATED BOTTOM TERMINAL		




TOP LINK TERMINAL DETAIL



MOUNTING FLANGE DETAIL



ALIGNMENT DIAGRAM
TOP VIEW



BOTTOM TERMINAL DETAIL
SILVER PLATED

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION	SCALE 1/8
----------	-----------

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER