



PCORE
ELECTRIC

KV CLASS 34.5kV **BIL** 200 kV **Uy** 22 kV

CURRENT RATING

400A DRAW LEAD CONN. IN 55°C RISE OIL
1200A BOTTOM CONNECTION IN 55°C RISE OIL

MIN. CREEP 41.00 [1041.4] **MIN. STRIKE** 17.00 [431.8]

CREEP/L-G 2.06 [52.3] **STD.** IEEE C57.19.00

PCB CONTENT OF OIL IS LESS THAN 1 ppm

DWG. **CATALOG NUMBER** **GLAZE COLOR**

SD B-89393-54 BROWN

SD B-89393-54-70 LT. GRAY



TITLE

IEEE STANDARD BUSHING


PRC BUSHING

1 1/8-12 THREAD TOP TERMINAL


NOTE: ACTUAL DRAW-LEAD CURRENT RATING IS DETERMINED BY CABLE SIZE



DRAW LEAD ASSEMBLY



MOUNTING FLANGE DETAIL



**FLANGE ALIGNMENT DIAGRAM
TOP VIEW**

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION

NET WEIGHT WAS 69 lb

SCALE 1/5

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER