



PCORE
ELECTRIC

KV CLASS 69 kV **BIL** 350 kV **Uy** 44 kV

CURRENT RATING

2000 AMP BOTTOM CONNECTION

DWG. **CATALOG NUMBER** **GLAZE COLOR**

SD	B-89523-256	BROWN
SD	B-89523-256-70	LT. GRAY

TITLE

PRC BUSHING

Ø1.00 [25.4] SLOTS ON 10.00 [254.0] B.C.
1.50 [38.1] LONGER BELOW FLANGE
BLADE TYPE BOTTOM TERMINAL

DATE 10-14-09 **REV. DATE** 8-18-21

MAXIMUM ALTITUDE 10000 ft [3000 m]



NET WEIGHT 205 lb [93 kg]

ANGLE OF INCLINATION FROM THE VERTICAL 0° TO 70°


MIN. CREEP 69.50 [1765.3] **MIN. STRIKE** 30.00 [762.0]

CREEP/L-G 1.74 [44.3] **STD.** IEEE C57.19.00/01

PCB CONTENT OF OIL IS LESS THAN 1 ppm



MOUNTING FLANGE DETAIL



**FLANGE ALIGNMENT DIAGRAM
TOP VIEW**

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION CREEP/L-G WAS CREEP/Uy, CORRECTED ROUNDING, NET WEIGHT WAS 152 lb [69 kg]

SCALE 1/6

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER