



kV CLASS	69 kV	BIL	350 kV	Uy	44 kV
CURRENT RATING					
1200 AMP BOTTOM CONNECTION					
MIN. CREEP	69.50 [1765.3]	MIN. STRIKE	30.00 [762.0]		
CREEP/L-G	1.74 [44.3]	STD.	IEEE C57.19.00/01		
PCB CONTENT OF OIL IS LESS THAN 1 ppm					

DWG.	CATALOG NUMBER	GLAZE COLOR
SD	B-89593-200	BROWN
SD	B-89593-200-70	LT. GRAY


DATE	4-12-00	REV. DATE	8-19-21
MAXIMUM ALTITUDE	10000 ft [3000 m]		
NET WEIGHT	160 lb [73 kg]		
ANGLE OF INCLINATION FROM THE VERTICAL	0° TO 70°		

TITLE	IEEE STANDARD BUSHING PRC BUSHING
--------------	--------------------------------------


QUICK-LINK BOTTOM CONNECTION
JOINT .75 [19.0] ABOVE FLANGE
MOUNTING SURFACE,
UNPLATED BOTTOM TERMINAL




ALIGNMENT DIAGRAM
TOP VIEW



TOP LINK TERMINAL DETAIL



MOUNTING FLANGE DETAIL



BOTTOM TERMINAL DETAIL

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION CREEP/L-G WAS CREEP/Uy, CORRECTED ROUNDING

SCALE 1/8

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER