



MATERIAL:

CAST CU. ALLOY

ACCOMMODATES:

#1 STR 8,33 (.328) DIA TO 4/0 STR
13,4 (.528) DIA CU/AL CABLES

NOMINAL INSTALLATION TORQUE:

45 IN-LBS FOR 1/4" DIA
HARDWARE

MARKING:

BURNDY
GCM28CG3
1 - 4/0 CU. AL.

FINISH:

ELECTRO-TINNED

COPYRIGHT. BURNDY INC. 1991

| | | | | | |
|---|-----------------------------------|---|--|-------------------------------|-------------------|
| <p>THIS DRAWING IS DUAL DIMENSIONED ALL DIMENSIONS IN MILLIMETRES AND INCHES EG. 25.4 MM OR 25.4 MM. (1.00 INCH) ORIGINAL DESIGN BASED ON INCH SYSTEM</p> | <p>THIRD ANGLE PROJECTION</p> | <p>GROUND CLAMP</p> | | | |
| | | <p>TYPE GCM28CG3</p> | | <p>SCALE 1:1</p> | |
| <p>THIS DRAWING AND/OR SPECIFICATION IS THE PROPERTY OF BURNDY INC. IT IS ISSUED IN STRICT CONFIDENCE, AND SHALL NOT BE REPRO- DUCED, OR COPIED, OR DISCLOSED TO OTHERS, OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT THE PERMISSION OF THE OWNER.</p> | | <p>DRAWN V.S.T. 5-1-91</p> | | <p>CHECKED L. KENYON</p> | |
| <p>REV. DATE REVISION DESCRIPTION BY C'KD.</p> | | <p>BURNDY an FCI Company 1530 BIRCHMOUNT ROAD, SCARBORO, ONTARIO</p> | | <p>DWG. NO. CSC 32005</p> | <p>REV. 0</p> |

D.O. No. 910427

APPROVED BY:

L. Kenyon-Guil 2/2/91