



Ø1 1/2 [38] TEMPORARY SERVICE DOOR

Ø1 1/2 [38] TEMPORARY SERVICE DOOR

- NOTES:**
1. BASE AND DOME ARE HDPE STRUCTURAL FOAM
 2. COLOR TO BE MUNSSELL GREEN.
 3. LOCKING HARDWARE TO BE STAINLESS STEEL.

CUSTOMER APPROVAL
 APPROVED BY: _____
 DATE: _____

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.		VERSION	LOG
REV	DATE	7.5#	IC
01	8/18/14	3.4 kg	S
DATE			
BY			
CHKD			
ENGR			
APPR			
DATE			
PROJECT	1 OF 1	DRAWING DESCRIPTION	REV
		11 X 12 X 28	B
		ABOVE GRADE PEDISTAL	2/16
		CREATING NUMBER	
		AG101015HD	



Hubbell
 11 X 12 X 28
 ABOVE GRADE PEDISTAL