

4

3

2

1

ITEM NO.	DESCRIPTION	QTY.
1	POLE MOUNT BRACKET	2
2	U-BOLT	2
3	M6 WASHER	4
4	M6 NUT	4
5	NUT	1
6	STUD	1
7	ATS-200 COAXIAL CABLE	4
8	N-PLUG	1

UNLESS OTHERWISE SPECIFIED:		NAME	DATE
DIMENSIONS ARE IN INCHES(MM).		DRAWN	MA 1/5/24
TOLERANCES:		CHECKED	IA 1/5/24
ANGULAR: MACH±1° BEND ±1°		ENG APPR.	
.XX = ±.01 (.25)		MFG APPR.	
.XXX = ±.005 (.127)		COMMENTS:	
INTERPRET GEOMETRIC TOLERANCING PER: ASME Y14.5M-2018			
PROJECT REF. 202-23			
MATERIAL MULTIPLE			
FINISH NA			
DO NOT SCALE DRAWING			

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF HUBBELL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF HUBBELL IS PROHIBITED.

AccelTex Solutions 12000 Crownpoint Dr., Suite 165 San Antonio, TX 78233	
TITLE: 2.4/5/6 GHz 4/7/7 dBi 4 Element Indoor/Outdoor Patch Antenna with N-STYLE ATS-OP-2456-477-4NP-36	
SIZE C	DWG. NO. ATS-03673
SCALE: 1:3	WEIGHT:
REV 1	SHEET 1 OF 1

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
1			INITIAL RELEASE		
REVISIONS					

4

3

2

1