




JUN 26 1997

DWG. DATE 6-2-97		REV. DATE		TITLE		DWG.	CATALOG NUMBER	UPPER PORCELAIN GLAZE COLOR
MIN. CREEP 17.00 (432)		KV CLASS 15 kV		7.25 (184) B.C. M22 THREAD AT BOTTOM END		SD	B 89111 109	CHOCOLATE
CREEPAGE PER Uy 1.70 (43)		Uy 10 kV		TEST STANDARD IEEE		SD	B 89111 109 /0	LT. GRAY No. 70
MIN. STRIKE DIST. 9.50 (241)		BIL 110 kV		ANGLE INCLINATION FROM VERTICAL = 0° 10° 10°		CURRENT RATING		
						1200 AMP BOTTOM CONN. @ 95°C MAX. OIL TEMPERATURE		



MOUNTING FLANGE

FLANGE ALIGNMENT DIAGRAM
TOP VIEW

DIMENSIONS IN INCHES (MILLIMETERS)

7A2A

LAST REVISION

NOTE TO PURCHASER
ALL SALES OF LAPP PRODUCTS ARE
SUBJECT TO OUR STANDARD TERMS
AND CONDITIONS AND THE LIMITED
WARRANTIES THEREUNDER