

1/2-13 UNC CORROSION
RESISTANT INSERT
4 PLACES

77 3/4
[1975]

53 3/4
[1365]

1/2-13 UNC
LIFTING BOLT
4 PLACES

48
[1219]


54 3/4
[1391]

77 3/4
[1975]

INTEGRAL BOTTOM

NOTE:

1. THIS BOX IS RATED FOR ANSI/SCTE 77
TIER 8 APPLICATIONS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.				 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
DRN	BY	DATE	WEIGHT		LC
CHK	APR	11/17/11	464# 210kg	S	
ENG			SCALE	REV	
APR	M&F	11/17/11	NTS	A	
APR			SIZE	11/11	
PROJECT NUMBER			DRAWING DESCRIPTION		
104726			QUAZITE® 48 X 72 X 48 BOX W/INTEGRAL BOTTOM STANDARD VERSION		
SHEET 1 OF 1			DRAWING NUMBER		
			B1A487248B		