

1/2-13 UNC CORROSION
RESISTANT INSERT
4 PLACES

42 7/8
[1069]

99 1/8
[2518]

INTEGRAL BOTTOM

1/2-13 UNC
LIFTING BOLT
4 PLACES


36
[914]

100 1/4
[2546]

43 3/4
[1111]

NOTES:

- THIS BOX IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.						
DRN	BY	DATE	WEIGHT		3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
			818# 371kg			LC
CHK			SCALE	DRAWING DESCRIPTION QUAZITE® 36 X 96 X 36 BOX INTEGRAL BOTTOM STANDARD VERSION		REV
ENG			NTS			A
APR			SIZE			
APR			B			4/13
PROJECT NUMBER				DRAWING NUMBER		
SHEET 1 OF 1				B1B369636B		