

1/2-13 UNC CORROSION
RESISTANT INSERT
4 PLACES

42 7/8
[1069]

99 1/8
[2518]

INTEGRAL BOTTOM

1/2-13 UNC
LIFTING BOLT
4 PLACES

48
[1219]


100 1/4
[2546]

NOTES:

- THIS BOX IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.

43 3/4
[1111]

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
CHK	ENG	APR	858# 389kg		LC S
APR	APR		SCALE	DRAWING DESCRIPTION QUAZITE® 36 X 96 X 48 BOX INTEGRAL BOTTOM STANDARD VERSION	REV
			NTS		A
			SIZE		4/13
PROJECT NUMBER			B	DRAWING NUMBER	
				SHEET 1 OF 1	B1B369648B