

1/2-13 UNC CORROSION
RESISTANT INSERT
4 PLACES

84 3/8
[2143]

54 3/8
[1381]

24
[610]

BOTTOM OPENING
47 [1194] X
77 [1956]


1/2-13 UNC
LIFTING BOLT
4 PLACES

54
[1372]

84
[2134]

NOTES:

1. THIS BOX IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.

| DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED. | | | | | | |
|---|-----|--------|---------------|---|----------------|------|
| DRN | BY | DATE | WEIGHT |  3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com | LOC | |
| | | | 439# 199kg | | OB | |
| CHK | ARN | 5/5/10 | SCALE | DRAWING DESCRIPTION CDR™ 48 X 78 X 24 BOX STANDARD VERSION | REV | |
| ENG | | | NTS | | A | |
| APR | M&F | 5/6/10 | SIZE | | | |
| APR | | | B | | | 5/10 |
| PROJECT NUMBER | | | | | DRAWING NUMBER | |
| | | | | | B1B487824A | |
| | | | | SHEET 1 OF 1 | | |