

1/2-13 UNC CORROSION
RESISTANT INSERT
4 PLACES

77 3/4
[1975]

53 3/4
[1365]

1/2-13 UNC
LIFTING BOLT
4 PLACES

48
[1219]


BOTTOM OPENING
47 3/4 [1213] X
70 3/4 [1797]

77 3/4
[1975]

54 3/4
[1391]

NOTES:

1. THIS BOX IS RATED FOR ANSI/SCTE 77 TIER 22 APPLICATIONS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.				 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com		LOC
DRN	BY	DATE	WEIGHT			OB
	BPH	6/25/10	467# 211kg			S
CHK			SCALE	DRAWING DESCRIPTION		REV
ENG			NTS	CDR™ 48 X 72 X 48 BOX		A
APR			SIZE	STANDARD VERSION		
APR			B			6/10
PROJECT NUMBER				DRAWING NUMBER		
				SHEET 1 OF 1		B1C487248A