

1/2-13 UNC CORROSION
RESISTANT INSERT
4 PLACES

84 3/8
[2143]

54 3/8
[1381]

24
[610]

BOTTOM OPENING
47 [1194] X
77 [1956]


1/2-13 UNC
LIFTING BOLT
4 PLACES

54
[1372]

84
[2134]

NOTES:

1. THIS BOX IS RATED FOR ANSI/SCTE 77 TIER 22 APPLICATIONS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.						
DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC	
			439# 199kg		OB	
CHK			SCALE	DRAWING DESCRIPTION CDR™ 48 X 78 X 24 BOX STANDARD VERSION	REV	
ENG			NTS		A	
APR			SIZE			
APR			B			6/10
PROJECT NUMBER					DRAWING NUMBER	
					B1C487824A	
				SHEET 1 OF 1		