


Post	P250048S0390	1
Suspension	S025049S0000	1
Anchor Shackle	AS-50	2
Part Number		Qty

REV DATE 02/04/10



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C2911-1989


DRY 60 HZ FLASHOVER	460
WET 60 HZ FLASHOVER	410
IMPULSE POSITIVE FLASHOVER	650
IMPULSE NEGATIVE FLASHOVER	720

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	305
IMPULSE POSITIVE WITHSTAND	585
IMPULSE NEGATIVE WITHSTAND	680

MAX WORKING LOADS, LBS(KN)

VERTICAL	10270 (45.6)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	7500 (33.3)
LEAKAGE DISTANCE	126
STRIKE DISTANCE	43


HUBBELL POWER SYSTEMS
 TITLE: QUADRI SIL BRACED LINE POST ASSY
 SIZE: B
 DWG NO: BLP048P0000
 CAT / PART / ASSY NO: BLP048P0000
 DWN BY: JVR
 DATE: 03/31/08
 SHEET 1 OF 1

CONFIDENTIAL THE DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE INFORMATION CONTAINED HEREIN IS UNCLASSIFIED FOR THE USE OF THE HUBBELL POWER SYSTEMS. UNLESS OTHERWISE SPECIFIED, ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.