



Mounting Base Detail

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C29.11-1988

DRY 60 HZ FLASHOVER	755
WET 60 HZ FLASHOVER	670
IMPULSE POSITIVE FLASHOVER	1175
IMPULSE NEGATIVE FLASHOVER	1270

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	500
IMPULSE POSITIVE WITHSTAND	1055
IMPULSE NEGATIVE WITHSTAND	1140

MAX WORKING LOADS, LBS(KN)

VERTICAL	9960 (44.2)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	930 (4.1)
LEAKAGE DISTANCE	208
STRIKE DISTANCE	76

Post	P250080S0420	1
Suspension	S025084S000A	1
Anchor Shackle	AS-50	2
Part Number		Qty

REV DATE 03/31/08

**OHIO BRASS**  
TOLERANCE CHART

**HUBBELL POWER SYSTEMS**

QUADRI SIL BRACED LINE POST ASSY

DO NOT SCALE THIS DRAWING

DATE 03/31/08

SHEET 1 OF 1