



Notes:

- Matt- Connector - "255 Alloy Electrical Bronze
Hardware - Silicon Bronze
- * ITEMS WITH ASTERISK HAS 3 BOLT STUD CLAMPING AND 6 BOLT IPS CLAMPING.

REV. NO.	DATE	DESCRIPTION
1	1-2-56	ADD 1-10-56
2	1-2-56	ADD 1-10-56
3	1-2-56	ADD 1-10-56
4	1-2-56	ADD 1-10-56
5	10-20-63	ADD 1-10-56

CATALOG	NUMBER	CONDUCTOR SIZES			DIMENSIONS IN INCHES					
		STUD		IPS	A	B	B-90	C	D	J
		DIA.	THDS							
DST	DST-90									
DST-0404-13-3	DST-0404-90-13-3	1/2"	13	1/2"	2	5 1/4	3 5/8	2 1/2	2 1/4	3/8
DST-0406-13-3	DST-0406-90-13-3	1/2"	13	3/4"	2	5 1/4	3 7/8	2 1/2	2 1/2	3/8
DST-0406-13	DST-0406-90-13	1/2"	13	3/4"	2	5 1/4	4 1/8	2 1/2	3	1/2
DST-0410-13-3	DST-0410-90-13-3	1/2"	13	1"	2	5 1/4	4	2 1/2	2 7/8	3/8
DST-0410-13	DST-0410-90-13	1/2"	13	1"	2	5 1/4	4 1/8	2 1/2	3 1/4	1/2
DST-0604-16-3	DST-0604-90-16-3	3/4"	16	1/2"	2	5 1/4	3 5/8	2 1/2		3/8
DST-0606-16-3	DST-0606-90-16-3	3/4"	16	3/4"	2	5 1/4	3 7/8	2 1/2	2 1/2	3/8
DST-0606-16	DST-0606-90-16	3/4"	16	3/4"	2	5 1/4	4 1/8	2 1/2	3	1/2
DST-0610-16-3	DST-0610-90-16-3	3/4"	16	1"	2	5 1/4	4	2 1/2	2 7/8	3/8
DST-0610-16	DST-0610-90-16	3/4"	16	1"	2	5 1/4	4 1/8	2 1/2	3 1/4	1/2
DST-1004-14-3	DST-1004-90-14-3	1"	14	1/2"	2	5 1/4	3 1/2	2 1/2	2 3/16	3/8
DST-1006-14-3	DST-1006-90-14-3	1"	14	3/4"	2	5 1/4	3 1/2	2 1/2	2 1/2	3/8
DST-1006-14	DST-1006-90-14	1"	14	3/4"	2	5 1/4	4 1/8	2 1/2	3	1/2
DST-1010-14-3	DST-1010-90-14-3	1"	14	1"	2	5 3/4	4	2 1/2	2 7/8	3/8
DST-1010-14	DST-1010-90-14	1"	14	1"	2	5 1/4	4 1/8	2 1/2	3 1/4	1/2
DST-1012-14	DST-1012-90-14	1"	14	1 1/4"	2 1/2	5 1/4	4 15/16	2 3/4	3 11/16	1/2
DST-1008-12-3	DST-1008-90-12-3	1"	12	3/4"	2	5	3 1/2	2 1/2	2 1/2	3/8

STUD CONNECTOR
TYPES DST & DST-90

C-2985

CATALOG	NUMBER	CONDUCTOR SIZES			DIMENSIONS IN INCHES					
		STUD		IPS	A	B	B-90	C	D	J
		DIA.	THDS							
DST-1106-12	DST-1106-90-12	1 1/8"	12	3/4"	2	5 1/4	4 1/8	2 1/2	3	1/2
DST-1110-12-3	DST-1110-90-12-3	1 1/8"	12	1"	2	5 1/4	4	2 1/2	2 7/8	3/8
DST-1110-12	DST-1110-90-12	1 1/8"	12	1"	2	4 3/4	4 1/4	2 1/2	3 1/4	1/2
DST-1112-12	DST-1112-90-12	1 1/8"	12	1 1/4"	2 1/8	5 7/16	4 3/8	2 3/4	3 9/16	1/2
DST-1206-12-3	DST-1206-90-12-3	1 1/4"	12	3/4"	2	5 1/4	3 7/8	2 1/2	2 1/2	3/8
DST-1206-12	DST-1206-90-12	1 1/4"	12	3/4"	2	5 1/4	4 1/8	2 1/2	3	1/2
DST-1210-12-3	DST-1210-90-12-3	1 1/4"	12	1"	2	5 1/4	4	2 1/2	2 7/8	3/8
DST-1210-12	DST-1210-90-12	1 1/4"	12	1"	2	5 1/4	4 9/32	2 1/2	3 3/16	1/2
DST-1212-12	DST-1212-90-12	1 1/4"	12	1 1/4"	2	5 1/2	4 15/32	2 3/4	3 9/16	1/2
DST-1214-12	DST-1214-90-12	1 1/4"	12	1 1/2"	2	5 1/2	4 19/32	2 3/4	3 13/16	1/2
DST-1406-12-3	DST-1406-90-12-3	1 1/2"	12	3/4"	2	5 1/4	3 7/8	2 1/2	2 1/2	3/8
DST-1406-12	DST-1406-90-12	1 1/2"	12	3/4"	2 1/4	5 3/16	4 1/16	2 1/2	3	1/2
DST-1410-12-3	DST-1410-90-12-3	1 1/2"	12	1"	2	5 1/4	4	2 1/2	2 7/8	3/8
DST-1410-12	DST-1410-90-12	1 1/2"	12	1"	2	5 1/4	4 3/16	2 1/2	3 3/16	1/2
DST-1412-12	DST-1412-90-12	1 1/2"	12	1 1/4"	2	5 1/2	4 3/8	2 3/4	3 5/8	1/2
DST-1414-12	DST-1414-90-12	1 1/2"	12	1 1/2"	2	5 7/16	4 1/2	2 3/4	3 9/16	1/2
DST-1420-12	DST-1420-90-12	1 1/2"	12	2"	2	5 9/16	4 13/16	2 3/4	4 1/2	1/2
DST-1606-12	DST-1606-90-12	1 3/4"	12	3/4"	2	5 1/4	4 1/8	2 1/2	3	1/2
DST-1610-12	DST-1610-90-12	1 3/4"	12	1"	2	5 1/4	4 1/4	2 1/2	3 1/4	1/2
DST-1612-12	DST-1612-90-12	1 3/4"	12	1 1/4"	2	5 1/2	4 3/8	2 3/4	3 5/8	1/2
DST-1614-12	DST-1614-90-12	1 3/4"	12	1 1/2"	2	5 9/16	4 1/2	2 3/4	3 7/8	1/2
DST-1620-12	DST-1620-90-12	1 3/4"	12	2"	2	5 5/16	4 15/16	3 1/4	4 1/2	1/2
DST-2010-12	DST-2010-90-12	2"	12	1"	1 7/8	5 3/8	4 3/8	2 1/2	3 3/16	1/2
DST-2012-12	DST-2012-90-12	2"	12	1 1/4"	2	5 5/8	4 1/2	2 3/4	3 3/16	1/2
DST-2014-12	DST-2014-90-12	2"	12	1 1/2"	2	5 5/8	4 11/16	2 3/4	3 11/16	1/2
DST-2020-12	DST-2020-90-12	2"	12	2"	2	6 1/8	5	3 1/4	4 1/2	1/2
DST-2024-12	DST-2024-90-12	2"	12	2 1/2"	1 7/8	6 1/8	5 1/4	3 1/4	4 3/4	1/2
DST-2210-12	DST-2210-90-12	2 1/4"	12	1"	2	5 3/8	4 5/8	2 1/2	3 3/16	1/2
DST-2212-12	DST-2212-90-12	2 1/4"	12	1 1/4"	1 7/8	5 5/8	4 5/8	2 3/4	3 5/8	1/2
DST-2214-12	DST-2214-90-12	2 1/4"	12	1 1/2"	1 7/8	5 5/8	4 3/4	2 3/4	3 7/8	1/2
DST-2220-12	DST-2220-90-12	2 1/4"	12	2"	1 7/8	6 1/8	5	3 1/4	4 1/2	1/2
DST-2224-12	DST-2224-90-12	2 1/4"	12	2 1/2"	1 7/8	6 1/8	5 1/4	3 1/4	4 7/8	1/2
DST-0504-11-3	DST-0504-90-11-3	5/8	11	1/2"	2	5 3/16		2 1/2	2 3/16	3/8
DST-2410-12	DST-2410-90-12	2 1/2"	12	1"	2 3/8	5 7/8	4 7/8	2 1/2	3 1/4	1/2
DST-2412-12	DST-2412-90-12	2 1/2"	12	1 1/4"	2 3/8	6 1/8	5 1/8	2 3/4	3 5/8	1/2
DST-2414-12	DST-2414-90-12	2 1/2"	12	1 1/2"	2 3/8	6 1/8	5 1/4	2 3/4	3 7/8	1/2

STUD CONNECTOR
 TYPES DST & DST-90

ANDERSON BRASS WORKS, INC.
 BIRMINGHAM, ALABAMA
 CAT. NO. DWG. NO. C-2985
 SH.# 2 of 4

-20-54
 DST CRD BY W.A.S.
 10

CATALOG	NUMBER	CONDUCTOR SIZES			DIMENSIONS IN INCHES							
		DST	DST-90	STUD		IPS	A	B	B90	C	D	J
				DIA.	THDS							
DST-2420-12	DST-2420-90-12	2 1/2"	12	2"	2 3/8	6 5/8	5 1/2	3 1/4	4 1/2	1/2		
DST-2424-12	DST-2424-90-12	2 1/2"	12	2 1/2"	2 3/8	6 5/8	5 3/4	3 1/4	4 7/8	1/2		
DST-2430-12	DST-2430-90-12	2 1/2"	12	3"	2 3/8	6 7/8	6 1/4	3 1/2	5 11/16	5/8		
DST-3012-12	DST-3012-90-12	3"	12	1 1/4"	2 7/8	6 5/8	5 5/8	2 3/4	3 5/8	1/2		
DST-3014-12	DST-3014-90-12	3"	12	1 1/2"	2 7/8	6 5/8	5 3/4	2 3/4	3 3/8	1/2		
DST-3020-12	DST-3020-90-12	3"	12	2"	3	7 1/8	6	3 1/4	4 1/2	1/2		
DST-3024-12	DST-3024-90-12	3"	12	2 1/2"	3	7 1/8	6 3/8	3 1/4	4 3/4	1/2		
DST-3030-12	DST-3030-90-12	3"	12	3"	3	7 3/8	6 1/16	3 1/2	5 11/16	5/8		
DST-3034-12	DST-3034-90-12	3"	12	3 1/2"	2 7/8	7 3/8	7 1/2	3 1/2	6 5/16	5/8		
DST-3040-12	DST-3040-90-12	3"	12	4"	2 7/8	7 7/8	7 11/16	4	6 15/16	5/8		
DST-3212-12	DST-3212-90-12	3 1/4"	12	1 1/4"	2 7/8	6 5/8	5 5/8	2 3/4	3 5/8	1/2		
DST-3214-12	DST-3214-90-12	3 1/4"	12	1 1/2"	2 7/8	6 5/8	5 3/4	2 3/4	3 7/8	1/2		
DST-3220-12	DST-3220-90-12	3 1/4"	12	2"	2 7/8	7 1/8	6	3 1/4	4 1/2	1/2		
DST-3224-12	DST-3224-90-12	3 1/4"	12	2 1/2"	2 7/8	7 1/8	6 1/4	3 1/4	4 7/8	1/2		
DST-3230-12	DST-3230-90-12	3 1/4"	12	3"	2 7/8	7 3/8	6 3/4	3 1/2	5 7/8	5/8		
DST-3234-12	DST-3234-90-12	3 1/4"	12	3 1/2"	2 7/8	7 3/8	7	3 1/2	6 3/8	5/8		
DST-3240-12	DST-3240-90-12	3 1/4"	12	4"	2 7/8	7 7/8	7 1/4	4	7	5/8		
DST-3414-12	DST-3414-90-12	3 1/2"	12	1 1/2"	3 1/8	6 7/8	6	2 3/4	3 7/8	1/2		
DST-3420-12	DST-3420-90-12	3 1/2"	12	2"	3 1/8	7 3/8	6 1/4	3 1/4	4 1/2	1/2		
DST-3424-12	DST-3424-90-12	3 1/2"	12	2 1/2"	3 1/8	7 3/8	6 1/2	3 1/4	4 7/8	1/2		
DST-3430-12	DST-3430-90-12	3 1/2"	12	3"	3 1/8	7 5/8	7	3 1/2	5 7/8	5/8		
DST-3434-12	DST-3434-90-12	3 1/2"	12	3 1/2"	3 1/8	7 5/8	7 1/4	3 1/2	6 3/8	5/8		
DST-3440-12	DST-3440-90-12	3 1/2"	12	4"	3 1/8	8 1/8	7 1/2	4	7	5/8		
DST-4014-12	DST-4014-90-12	4"	12	1 1/2"	3 5/8	7 3/8	6 1/2	2 3/4	3 7/8	1/2		
DST-4020-12	DST-4020-90-12	4"	12	2"	3 5/8	7 7/8	6 3/4	3 1/4	4 1/2	1/2		
DST-4024-12	DST-4024-90-12	4"	12	2 1/2"	3 5/8	7 7/8	7	3 1/4	4 7/8	1/2		
DST-4030-12	DST-4030-90-12	4"	12	3"	3 5/8	8 1/8	7 1/2	3 1/2	5 7/8	5/8		
DST-4034-12	DST-4034-90-12	4"	12	3 1/2"	3 3/4	8 1/4	7 3/4	3 1/2	6 3/8	5/8		
DST-4040-12	DST-4040-90-12	4"	12	4"	3 5/8	8 5/8	8	4	7	5/8		
DST-1630-12	DST-1630-90-12	1 3/4"	12	3"	2	6 1/4	5 1/4	3 1/2	5 7/16	1/2		
DST-1624-12	DST-1624-90-12	1 3/4"	12	2 1/2"	2	6	7 3/8	3 1/4	4 3/4	1/2		
DST-1114-12	DST-1114-90-12	1 1/8"	12	1 1/2"	2 1/8	5 7/16	6 3/8	2 3/4	3 7/16	1/2		
DST-3210-12	DST-3210-90-12	3 1/4"	12	1"	2 7/8	6 3/8	5 1/2	2 1/2	3 3/16	1/2		
DST-3010-12	DST-3010-90-12	3"	12	1"	2 7/8	6 3/8	5 1/2	2 1/2	3 3/16	1/2		
DST-1430-12		1 1/2"	12	3"	2 1/4"	5 7/16		2 7/8	5 1/16	1/2		
DST-1124-12	DST-1124-90-12	1 1/8"	12	2 1/2"	2	5 7/16		2 3/4	4 5/16	1/2		

REVISIONS	NO.	DATE	DESCRIPTION
	3	7-20-72	DST-3034-90-12 B-90 WAS REVISED VARIOUS DIM. FOR COMP.
	4	10-26-79	

REVISIONS	NO.	DATE	DESCRIPTION
	1	6-24-70	DST-3040-90-12 7.7.62 WAS 7/4
	2	8-23-71	DST-2430-12 7/8 WAS 5/8

DATE: 1-20-54
 OWN IN ST. CKD BY: VAS
 APPROVED: [Signature]
 SCALE: [Signature]

STUD CONNECTOR
 TYPES DST & DST-90

R/27. ANDERSON BRASS WORKS
 BIRMINGHAM
 CAT. NO. C-2985
 SH. 3-2

