


**NOTES:**

1. LOGO TO BE SPECIFIED: \_\_\_\_\_
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 8,000 LBS. [35,584 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 12,000 LBS. [53,376 N].
3. FURNISHED W/(2) 1/2-13 UNC X 4 1/2 [114] LONG SS CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.						
	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-348-3062 www.quazite.com	LOC	
DRN	BSR	1/10/12	165# 75kg		OB	
CHK	MMR	1/11/12	SCALE		S	
ENG			NTS		REV	
APR			SIZE		A	
APR			B	1/12		
PROJECT NUMBER			DRAWING DESCRIPTION		DRAWING NUMBER	
105074			QUAZITE® 30 X 48 X 3 COVER STANDARD VERSION		C10304803A	
			SHEET 1 OF 1			