



**NOTES:**

1. LOGO TO BE SPECIFIED: \_\_\_\_\_.
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 22,500 LBS. [100,080 N].
3. FURNISHED W/(2) 1/2-13 UNC X 3 [76] LONG S.S. CAPTIVE PENTA HEAD BOLTS.
4. OLD P/N: C12-1622-02

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DESIGN	BY	DATE	WEIGHT	SCALE	LOGO
CHN	JR/T	6/8/10	34#	15K	HUBBELL
ENT	JR/T	6/10/10	NTS	1/2	QUAZITE® 16 X 22 X 02 COVER
APP	JR/T	6/21/10	B	STANDARD VERSION	REV B
PROJECT NUMBER			DRAWING NUMBER		
091269			C12162202A		
SHEET 1 OF 1			DATE 9/10		