



NOTES:

1. LOGO TO BE SPECIFIED: _____.
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 22,500 [100,085 N].
3. FURNISHED W/(2) 1/2-13 UNC X 3 [76] LONG S.S. CAPTIVE PENTA HEAD BOLTS.
4. OLD P/N: C12-3200-02

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DATE	BY	WEIGHT	DESCRIPTION	REV
9/16/10	999	141#	QUAZITTE® 32 ROUND COVER	OB
9/16/10	LLM/K	64kg	QUAZITTE® 32 ROUND COVER	S
9/16/10	LLM/K	NTS	QUAZITTE® 32 ROUND COVER	A
9/16/10	LLM/K	B	STANDARD VERSION	9/10
PROJECT NUMBER				10476
DRAWING NUMBER				C12320002A