



- NOTES:**
1. LOGO TO BE SPECIFIED: _____.
 2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,723 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 22,500 LBS. [100,085 N].
 3. FURNISHED W/(2) 1/2-13 UNC X 4 1/2 [114] LONG S.S. CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DATE	BY	WEB	LOGO
12/30/10	6332	333	OB
12/30/10	1510	1510	S
DATE	BY	WEB	LOGO
12/30/10	6332	333	OB
12/30/10	1510	1510	S

QUAZITE 36 X 60 X 03 COVER
 STANDARD VERSION
 102555
 SUBJECT 1 02 1
 DRAWING NUMBER C12366003A