



NOTES:

1. LOGO TO BE SPECIFIED: _____.
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,080 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 33,750 LBS. [150,120 N].
3. FURNISHED W/(2) 1/2-13 UNC X 3 [76] LONG S.S. CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

BY	DATE	WEIGHT	LOC
3/3/2	6/10/10	40#	S
CHK	6/10/10	18kg	B
ENG	6/22/10	SCALE	REV
APR	6/22/10	MMS	1/14
ESR OR PROJECT NUMBER	091651	DRAWING DESCRIPTION	QUAZITE® 13 X 24 X 02 COVER
SHEET	1 OF 1	DRAWING NUMBER	C16132402A
		STANDARD VERSION	
		3921 INDUSTRIAL PARK DR	
		LENOIR CITY, TN 37771	
		800-346-3062	
		www.quazite.com	
		HUBBELL	