



**NOTES:**

1. LOGO TO BE SPECIFIED: \_\_\_\_\_.
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 22,500 LBS. [100,080 N].
3. FURNISHED W/(2) 1/2-13 UNC X 3 [76] LONG SS CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DRN	RT	DATE	34#	WEIGHT	3621 INDUSTRIAL PARK DR	LOC
CHK	MEF	5/15/15	15kg	HUBBELL	LENOIR CITY, TN 37771	OB
ENG			SCALE	800-348-3062	www.quazite.com	S
APR			NTS	DRAWING DESCRIPTION		REV
			SIZE	QUAZITE $\phi$ 20 X 2 COVER		A
			B	STANDARD VERSION		9/15
ESR OR PROJECT NUMBER			111252	DRAWING NUMBER		
				C16200002A		
SHEET			1 OF 1			