



26
6601

1680


2
[51]

2X Ø7/8 [22] THRU HOLE W/Ø1 3/8 [35]
X 5/8 [16] DEEP COUNTERBORE

NOTES:

1. LOGO TO BE SPECIFIED:_____.

2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,080 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 33,750 LBS. [150,120 N].
3. FURNISHED W/(2) 1/2-13 UNC X 3 [76] LONG S.S. CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.									
	BY	DATE	100# WGT	 3621 INDUSTRIAL PARK DR LENOX CITY, TN 37771 909-346-3052 www.hubbell.com	DRAWN DESCRIPTION			LOG	
Part	3037	6/26/10	45kg		CDR™ 24 X 24 X 2 COVER			OB	
COIL			36 X 42					S	
IN			3/2					REV	
APP								A	
SER	B			STANDARD VERSION				9/10	
PROJECT NUMBER				SHEET 1 OF 1 DRAWING NUMBER C16242402A					