



2X Ø5/8 [16] THRU HOLE W/Ø1 1/4 [32]
X 1/2 [13] DEEP COUNTERBORE

1/2 [13] X 4 [102] PULL SLOT W/
Ø1/4 [6] CENTER PIN (2 PLACES)

35 5/8
[905]

24
[610]

LOGO

TIER 22

QUAZITE LOGO

SKID RESISTANT SURFACE

3 [76]

NOTES:

1. LOGO TO BE SPECIFIED: _____.
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,080 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 33,750 LBS. [150,120 N].
3. FURNISHED W/(2) 1/2-13 UNC X 4 [102] LONG S.S. CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

WEIGHT	94#	49kg	 7021 INDUSTRIAL PAPER DR ENGINE CITY, TN 37071 800-368-3062 www.hubbell.com	LOG	OB
BY	DATE	DATE		REV	A
DATE	3/31/09	6/28/10			
CHKD					
ENGR					
APPR					
DESIGN PROJECT NUMBER	1-02-1		DRAWING NUMBER	C16243603A	