



- NOTES:**
1. LOGO TO BE SPECIFIED: \_\_\_\_\_.
  2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,080 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 33,750 LBS. [150,120 N].
  3. FURNISHED W/(2) 1/2-13 UNC X 4 1/2 [114] LONG SS PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.		WEIGHT		DRAWING DESCRIPTION		PROJECT NUMBER	
BY	DATE	170#	77kg	HUBBELL® 36 X 36 X 3 COVER		SUBJECT 1-02-1	
CHKD	6/25/10	NTS	NTS	CDR™ 36 X 36 X 3 COVER		DRAWING NUMBER	
APPR				STANDARD VERSION		C16363603A	
				REV		DATE	
				A		6/10	

170# 77kg  
 HUBBELL®  
 36 X 36 X 3 COVER  
 STANDARD VERSION  
 CDR™ 36 X 36 X 3 COVER  
 1-02-1  
 C16363603A