

4X $\phi 7/8$ [22] THRU
W/ $\phi 1 3/8$ [35] X $5/8$ [16]
DEEP COUNTERBORE


4X $3/4$ [19] X 2 [51]
PICK HOLE

SKID RESISTANT SURFACE

QUAZITE LOGO

NOTES:

1. LOGO TO BE SPECIFIED: _____.
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 8,000 LBS. [35,548 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 12,000 LBS. [53,376 N]
3. FURNISHED W/ (4) $1/2-13$ X $4 1/2$ [114] LONG S.S. CAPTIVE PENTA HEAD BOLTS.
4. OLD P/N: C10-4848-23

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.					
DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
CHK	ENG	APR	271# 123kg		OB
APR	APR	5/04/10	SCALE	DRAWING DESCRIPTION QUAZITE® 48 X 48 X 03 COVER STANDARD VERSION	REV
			NTS		B
			SIZE		9/10
PROJECT NUMBER			DRAWING NUMBER		
			SHEET 1 OF 1		C1A484803A